

LevNet RF™ Receptacle

Wireless Solution for Plug Load Control Requirements

The Leviton LevNet RF Receptacle Receiver works in conjunction with EnOcean-enabled Energy Harvesting Wireless Lighting Control Products to provide an optimal solution for retrofit lighting needs. These wireless products combine Leviton's switching technology with self-powered and wireless technologies, developed and licensed from EnOcean®.

The RF Control System offers scalable, easy-to-install, remote control of appliances and lighting, as well as one-button scene lighting control to create the perfect ambiance.

APPLICATIONS

The RF Receptacle Receiver can be installed in place of traditional wall receptacles and fits in a standard single-gang wall box. No additional wiring is required. The receptacles are compatible with lamps, appliances and electronic loads. The RF Receptacle Receiver responds to signals from the RF transmitters switching the relay (controlling the load) on or off. Models include a duplex outlet design with either 1 or 2 controlled receptacles to provide local and remote switching of the lighting load ON/OFF.

MODELS

LevNet RF Split Duplex TR Receptacle:

- Top: Controlled
- Bottom: Continuously on

LevNet RF Duplex Receptacle:

- Top: Controlled
- Bottom: Controlled

FEATURES AND BENEFITS

- Controlled side can be used for wireless ON/OFF control of plugged-in electrical loads up to 15 amps such as lamps, appliances and electronics
- Tamper-resistant (TR) receptacle
- TR symbol on receptacle strap assures that it meets the 2008 NEC® code requirement
- Shutter mechanism inside the TR receptacle blocks access to the contacts unless a two-prong plug is inserted, helping ensure hairpins, keys, etc., will be locked out
- Green locator LED illuminates when load is ON
- Superior versatility provides several product options in one box: 5 changeable faceplates and single pole switch capability are included
- Responds to LevNet RF Transmitters as well as EnOcean certified transmitters from other manufacturers
- ON/OFF scene control compatibility
- Local and remote ON/OFF control of connected loads
- Transient surge protection to IEC Level 3
- ESD protection to 61000 4-2 Level 4 to protect against damage and memory loss due to static discharges



SPECIFICATIONS

Operating Temperature	0°C to 40°C, 32°F to 104°F
Relative Humidity	20% to 90% (non-condensing)
Terminations	3 screw terminals for line, neutral and ground
Listings	Complies with FCC Part 15, Class B; EnOcean Certified Switch; TR Receptacle: UL Listed (File #E-66800)
Warranty	Five-Year Limited Warranty

ORDERING INFORMATION

CAT. NO. *	DESCRIPTION	RATING
WSG15-0DZ	LevNet RF Split Duplex TR Receptacle with LED Locator	Controlled Side: 1800W, 1800VA, 1/2HP, 120V; Receptacle: NEMA 5-15R
WSG15-TDZ	LevNet RF Duplex Receptacle for Dual Controlled Outlet (CA Title 24)	Controlled Side: 1800W, 1800VA, 1/2HP, 120V

* Suffix (-Z) includes White, Ivory, Light Almond, Gray and Black Color Change Kit faceplates.

LevNet RF Receptacle

Leviton Mfg. Co., Inc. Lighting & Energy Solutions

201 N. Service Rd. Melville, NY 11747-3138 Tech Line: 1-800-824-3005 Fax: 1-800-832-9538 www.leviton.com/les
 © 2013 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.